



Nylon Convenience Adapters

NEMA Configuration

| Catalog Number | HBL2270 | HBL2271 | HBL2128 | HBL2274 | HBL2129 | HBL31CM29* |
|-----------------|----------------------------|-----------------------------|-----------------------------|-----------------------------|-----------------------------|-----------------------------|
| Male Blade End | 15A 125V NEMA 5-15P | 15A 125V NEMA 5-15P | 15A 125V NEMA 5-15P | 15A 125V NEMA L5-15P | 20A 125V NEMA L5-20P | 30A 125V NEMA L5-30P |
| Female Slot End | 20A 125V NEMA 5-20R | 15A 125V NEMA L5-15R | 20A 125V NEMA L5-20R | 20A 125V NEMA 5-20R | 20A 125V NEMA 5-20R | 20A 125V NEMA 5-20R |

Note: *Not UL Listed.

CAUTION: Where adapters have different ratings on the blade and slot end the following precautions must be exercised in their use.

- (1) Remember that overcurrent protection is determined by the blade end.
- (2) The use of the adapter should be limited to the lowest rated end of the adapter in order to prevent overheating.
- (3) Adapters do not provide GFCI, overcurrent or short circuit protection.



Plug In Adapters

| Description | Catalog Number |
|--|------------------|
| Male end - 2 wire parallel polarized blades, 15A, 125V. Female end - 3 wire 15A, 125V straight slot grounding. | HBL5273L |
| Male end - 3 wire crow foot 15A, 125V blades. Female end - 3 wire 15A, 125V straight slot grounding. | HBL5289♦* |
| Male end - 3 wire 10A, 250V, 15A, 125V Twist-Lock® blades. Female end - 3 wire 15A, 125V straight slot grounding. | 9053A♦* |
| Male end - 3 wire 15A, 125V straight blade grounding. Female end - 10A, 250V, 15A 125V Twist-Lock® slots. | 9054A♦* |

Note: ♦Must always be used with a grounded receptacle.

*Not UL Listed.

Fluorescent Starters

Neostart

The Hubbell Neostart is a glow discharge type of starter which combines fast starting speed with rugged, dependable operation. The Neostart lights the lamp very rapidly and insures proper lamp operation throughout rated life. Because of its rugged construction, it can be depended upon to withstand continued punishment resulting from lamp failure. In addition, it operates satisfactorily over a wide temperature range. In dual lamp circuits, the Neostart lights both lamps quickly and uniformly.

| Lamps | Catalog Number |
|--|----------------|
| 14, 15 and 20 watt lamps | FS2 |
| 13, 30 and 40 watt lamps | FS4 |
| 4, 6 and 8 watt lamps | FS5 |
| 22 watt circle line, 25 watt standard lamps | FS25 |

